

Dental Demo Teaching System JPS-FT-III

Details

Input Voltage: AC220V/50Hz, Power 200W

Noise level: ≤60dB

Two hand piece automatic control

3-way syringe

Air control and negative pressure suction system

Light intensity: 6000-25000 lux

Features

Designed for the simulation of clinical education, help students developthe right operating posture in the pre-dinical study, master ergonomicskills and then smoothly transition to real clinical treatment.

It can simulate four-hand operation in clinical Special needs of the clinical are taken into account in every detail design, The auto reset function of the shoulder system can provide the cleanliness and utilization of space.

Pitch: -5°to 90° Uft Max High position: 810mm, Min Low position: 350mm Fully simulate clinical operations

Marble countertop for easy cleaning Independent negative pressure system, external quick suction water bottle, easy to operate

WWW.JPSDENTAL.COM







JPSM 70

Customized solutions for advanced patient experience

Dental unit



I Details can be customized on preference I









